



UNCONTROLLED DOCUMENT

$\phi 5.00 \pm 0.38$ $\phi 3.20 \pm 0.26$



ALL DIMENSIONS ARE IN MILLIMETERS

TOLERANCES UNLESS NOTED

- ±.13MM ON DIMENSIONS THRU 15.88MM
- ±.20MM ON DIMENSIONS 15.89MM THRU 25.41MM
- ±.25MM ON DIMENSIONS 25.42MM THRU 38.10MM
- ±.38MM ON DIMENSIONS LARGER THAN 38.10MM

WE RESERVE THE RIGHT
TO DISCONTINUE ITEMS,
CHANGE SPECIFICATIONS
OR DESIGN AT ANY TIME
WITHOUT NOTICE AND
WITHOUT INCURRING
ANY OBLIGATIONS

PROPERTY OF		
MICRO PLASTICS INC.		
CATALOG DRAWING METRIC SPACER MICRO P/N 13ME021 DWG. # 13ME021 FILE SERVER\ENG\WEB		
MATERIAL: HEAT STABILIZED NYLON BLACK		
DATE	SCALE 12:1	TA