



**1 2D Views**

## 2 Configuration settings

Configuration	
Part Number	RWS-10-01BK
Description	Cable Clamps - Plug In, Round Wire Saddle - Black ; UL94 V-2
Material Flammability Standard	UL94 V-2
UL/CSA Description	UL E71558
Full Material	Nylon 6/6
Type	1
Style	1
Mounting Method	None
Minimum Compatible Panel Thickness (Seed)	0.030 in
Maximum Operating Temperature (Seed)	185 °F
Minimum Operating Temperature (Seed)	-40 °F
Maximum Compatible Cable Diameter (Seed)	0.625 in
Compatible Hole Size (Seed)	0.250 in
Maximum Compatible Panel Thickness (Seed)	0.060 in

Bill of Materials Data	
Manufacturer	Essentra Components
Description	Cable Clamps - Plug In, Round Wire Saddle - Black ; UL94 V-2
Part Number	RWS-10-01BK