

AideTek Automotive 5-in-1 Test Lead Kit Shielded Alligator Clips and Large Crocodile Clips TLP20159



Feature:

Test Lead Kit includes a basic set of interchangeable specialty test probes designed for automotive use.

The flexible back probing pins are great for sliding into automotive connectors like those on fuel injectors and MAP sensors.

The large crocodile clips are good for clipping to grounds and battery terminals.

Package Including:

- 1) Two(One red + one black) 32 inch PVC lead extensions, Shrouded banana plugs at both ends, Whole length: 82cm (32.22 inch)**
- 2) A pair of sharp Stainless Steel Needle Tipped Tip Multi-meter Probes Test Leads**
- 3) Two (one red + one black) modular 4 inch heavy duty test probe handles; Safety test probe with 4mm socket connection. Spring-loaded tip, Length: 10.5cm; Material: Insulator: PA; Body: Brass; Spring: Beryllium copper; Surface: Nickel plated; Rated voltage/current: CATII 1000V/Max.32A; 600v 1a 4mm Socket, Whole Length: 129.5mm Needle length: 20.5mm, Match with the test lead of Multi-meter or Oscilloscope Advantage:Lengthened sharp and hard stainless steel needle(Dia.1mm) can easily pierce the surface of cable but doesn't destroy it. It can be widely used about the non-destructive cable test in auto, Telecom, Industry or test inside of the plug. Color : Red Black Metal material : Brass 、 Stainless Steel Insulator material : PA Rated voltage/current: CE CATII 600V /MAX. 1A Connect method: 4mm socket connection**
- 4) A pair of one Black/Red small crocodile clips, Safety Sliver plated alligator clip Rated voltage/current CATII 300V 15A, Metal material : Brass; Insulator material : PA; whole size: 56mm(2.2 inch) max jaw size: 12mm(0.47 inch)**
- 5) A pair of one Black/Red large crocodile clips, Safety Sliver plated alligator clip Rated voltage/current: CATIII 1000V/Max.32A, Metal material: Brass; Insulator material: PA; whole size: 83.5mm(3.3 inch) max jaw size: 27mm(1.06 inch)**