POX BOX 2426 Monrovia CA 91016 USA Tel.: (408) 329-7985 Fax: (866)571-5680

www.aidetek.com support@aidetek.com

AideTek Automotive 6-in-1 Test Lead Insulation Piercing test clip TLP20163



Feature:

Test Lead Kit includes basic set of interchangeable specialty test probes designed for automotive use.

The flexible back probing pins are great for sliding into automotive connectors like those on fuel injectors and MAP sensors.

The large crocodile clips are good for clipping to grounds and battery terminals.

Package Including:

- 1. Two(One red + one black) 32 inch PVC lead extensions, Shrouded banana plugs at both ends, Whole length: 82cm (32.22 inch)
- 2. A pair of sharp Stainless Steel Needle Tipped Tip Multi-meter Probes Test Leads

600v 1a 4mm Socket, Whole Length: 129.5mm Needle length: 20.5mm, Match with the test lead of Multi-meter or Oscilloscope

Advantage: Lengthened sharp and hard stainless steel needle(Dia.1mm) can easily pierce the surface of cable but doesn't destroy it. It can be widely used about the non-destructive cable test in auto, Telecom, Industry or test inside of the plug. Color: Red Black Metal material: Brass Stainless Steel Insulator material: PA Rated voltage/current: CE CATII 600V /MAX. 1A Connect method: 4mm socket connection

- 3. Two (one red + one black) modular 4 inch heavy duty test probe handles; Safety test probe with 4mm socket connection. Spring-loaded tip, Length: 10.5cm; Material: Insulator: PA; Body: Brass; Spring: Beryllium copper; Surface: Nickel plated; Rated voltage/current: CATII 1000V/Max.32A;
- 4.A pair of one Black/Red large crocodile clips, Safety Sliver plated alligator clip Rated voltage/current: CATIII 1000V/Max.32A, Metal material: Brass; Insulator material: PA; whole size: 83.5mm(3.3 inch) max jaw size: 27mm(1.06 inch)
- 5. Insulation Piercing Clip Set, Banana Jack Accepts Banana Plug Leads with rigis insulation sleeve, Color: Red, Black, Length 4 In" (143cm), Stainless Steel Probe Pierces Insulation on Gauge Wire, Tip Material Stainless Steel, For Use With Banana Plug Test Leads, Accepts 4mm Banana Plugs, Includes (1) Red and (1)Black Probe

Pierces wire up to 4mm diameter

Spring loaded press pin of cooper, which can grasp the conductor of max 4mm thickness

Compatible with all Pomona / FLUKE banana plug leads

Sheathed 4mm receptacle accepts shrouded banana plugs and unshrouded banana plugs

Meets all the latest international safety standards

AideTek AideTek

POX BOX 2426 Monrovia CA 91016 USA Tel.: (408) 329-7985 Fax: (866)571-5680

www.aidetek.com support@aidetek.com

Current: 2 Amperes

Std. Colors: black, red

Operating voltage: CAT III 1000V; Current: 2 Amperes.

6. A pair of Safety test clip with 4mm socket connection. Flexible spring with the tube can contact the wires and terminals even at the corner. CATIII 1000V/Max.10A Material: Insulator:PA, Body:Brass

& Stainless steel