

Garant
Bi-hexagon socket deep, 1/2 inch imperial version, Width across flats: 3/8in

Order data

Order number	642532 3/8
GTIN	4062406310462
Item class	61A

Description
Version:

Forged from high quality steel, internally bevelled for easy fitting to bolt heads. Square socket drives with close tolerances for secure fit on the drive attachment.

Close tolerance widths across flats protects nuts and bolt heads. **Thin walls** for access to restricted places. Bi-hex **HT drive** profile protects the corners of nuts and bolt heads.

Material:

Chrome vanadium steel, chrome-plated.

Square drive: 1/2 in

Ø drive output end: 15.4 mm

Length: 77 mm

Technical description

Ø drive output end	15.4 mm
Length	77 mm
Width across flats	3/8 in
Square drive	1/2 in
Standard	DIN 3124
Standard	ISO 2725-1
Standard	ASME B 107.5M
Standard	DIN EN 3710

Standard	DIN EN 3709
Drive profile	Bi-hex socket
Material	HPQ® high performance steel
Surface	chrome-plated
with AS Drive profile.	yes
Type of product	Socket insert