

Garant
Bi-hexagon socket deep, 1/2 inch imperial version, Width across flats: 1/2in

Order data

| | |
|--------------|---------------|
| Order number | 642532 1/2 |
| GTIN | 4062406310486 |
| Item class | 61A |

Description
Version:

Forged from high quality steel, internally bevelled for easy fitting to bolt heads. Square socket drives with close tolerances for secure fit on the drive attachment.

Close tolerance widths across flats protects nuts and bolt heads. **Thin walls** for access to restricted places. Bi-hex **HT drive** profile protects the corners of nuts and bolt heads.

Material:

Chrome vanadium steel, chrome-plated.

Square drive: 1/2 in

Ø drive output end: 19.1 mm

Length: 77 mm

Technical description

| | |
|--------------------|---------------|
| Ø drive output end | 19.1 mm |
| Length | 77 mm |
| Width across flats | 1/2 in |
| Square drive | 1/2 in |
| Standard | DIN 3124 |
| Standard | ISO 2725-1 |
| Standard | ASME B 107.5M |
| Standard | DIN EN 3710 |

| | |
|------------------------|-----------------------------|
| Standard | DIN EN 3709 |
| Drive profile | Bi-hex socket |
| Material | HPQ® high performance steel |
| Surface | chrome-plated |
| with AS Drive profile. | yes |
| Type of product | Socket insert |