

Garant
Electronics side cutter for ferrous materials, kW, overall length: 135mm


Order data

| | |
|--------------|---------------|
| Order number | 726742 135 |
| GTIN | 4062406395032 |
| Item class | 71B |

Description

Version:

Professional diagonal side cutter with slightly shearing cut. Both cutter parts are very accurately put together using carefully machined holes and polished surfaces to ensure a precise cut. With opening spring and ergonomically designed handles for secure and comfortable use. **2-component grips** of dissipative material. **Suitable for ESD work.**

Material:

Made of carbon steel (C70), precision stamped and heat-treated, non-reflective phosphate.

Material: Carbon steel (C70)

Head width: 13.5 mm

Cutter length: 8 mm

Cutting capacity copper wire up to Ø: 2 mm

Technical description

| | |
|--------------------------------------|--------------------|
| Cutter length | 8 mm |
| overall length | 135 mm |
| Head width | 13.5 mm |
| Cutting capacity copper wire up to Ø | 2 mm |
| electrostatic characteristic | EGB/ESD |
| Cutting chamfer | without bevel |
| Material | Carbon steel (C70) |

| | |
|------------------------|----------------------------|
| Surface | phosphated, non-reflecting |
| Product name attribute | kW |
| with return spring | yes |
| Type of product | Cutting pliers |