

Garant
Electronics end cutter, SFW, overall length: 130 mm

Order data

Order number	726922 130
GTIN	4062406395056
Item class	71B

Description
Version:

Professional diagonal side cutters with slightly shearing cut. Both cutter parts are very accurately put together using carefully machined holes and polished surfaces to ensure a precise cut. With opening spring and ergonomically designed handles for secure and comfortable use. **2-component grips** of dissipative material. **Suitable for ESD work.**

Material:

Made of carbon steel (C70), precision stamped and heat-treated, non-reflective phosphate.

Cutting chamfer: very fine bevel

Head length: 10 mm

Head width: 10 mm

Cutting capacity copper wire up to Ø: 0.6 mm

Technical description

Cutting capacity copper wire up to Ø	0.6 mm
Head width	10 mm
Head length	10 mm
electrical insulation	EGB/ESD
Cutting chamfer	very fine bevel
Material	Carbon steel (C70)
Surface	phosphated, non-reflecting

Product name attribute	SFW
Type of product	Cutting pliers