

Electronics snipe-nose pliers with long jaws, overall length: 155 mm



Order data

Order number	727162 155
GTIN	4062406395087
Item class	71B

Description

Version:

The jaws of the cutter are accurately put together using carefully machined holes and polished surfaces. With opening spring and ergonomically designed handles for secure and comfortable use. **2–component** conductive grips, **suitable for ESDs**.

Snipe-nose, serrated internal jaws.

Material:

Made of carbon steel (C70), precision stamped and heat-treated, non-reflective phosphate.

electrical insulation: EGB/ESD

Head width: 13 mm Jaw length: 32 mm

Technical description

overall length	155 mm
Head width	13 mm
Jaw length	32 mm
electrostatic characteristic	EGB/ESD
Type of jaws	Flat pointed, serrated internal jaws
Handle	2-component grip
Material	Carbon steel (C70)
Surface	phosphated, non-reflecting

Data sheet

⚠ Hoffmann Group

with return spring	yes
Type of product	Snipe nose pliers