

Electronics needle-nose pliers 48° angled, overall length: 150 mm



Order data

| Order number | 727182 150 |
|--------------|---------------|
| GTIN | 4062406395094 |
| Item class | 71B |

Description

Version:

The jaws of the cutter are accurately put together using carefully machined holes and polished surfaces. With opening spring and ergonomically designed handles for secure and comfortable use. 2-component conductive grips, suitable for ESDs.

Needle-nose, serrated internal jaws.

Material:

Made of carbon steel (C70), precision stamped and heat-treated, non-reflective phosphate.

electrical insulation: EGB/ESD

Head width: 13 mm Jaw length: 35 mm

Technical description

| overall length | 150 mm |
|------------------------------|------------------------------------|
| Head width | 13 mm |
| Jaw length | 35 mm |
| electrostatic characteristic | EGB/ESD |
| Jaw design | angled |
| Type of jaws | Snipe-nose, serrated internal jaws |
| Handle | 2-component grip |
| Material | Carbon steel (C70) |

| Surface | phosphated, non-reflecting |
|--------------------|----------------------------|
| with return spring | yes |
| Type of product | Snipe nose pliers |