

Garant**LED rechargeable pen light, Type: 200****Order data**

Order number	081448 200
GTIN	4062406401900
Item class	01A

Description**Version:**

Extremely slim rechargeable LED pen torch with sturdy and elegant aluminium casing. The steplessly dimmable main beam, and the strongly focussed spotlight LED ensure optimum illumination in restricted spaces.

- **Sturdy metal clip on the back.**
- **Strong magnet in the lamp base.**
- **Battery charge is always clearly visible through the central LED display.**

Function:

IP30: Protected against penetration by foreign bodies with $\varnothing > 2.5$ mm, however tools and wires should be kept away, and offers no protection against water.

Supplied with:

Supplied with USB-C charging cable.

IP Index of Protection: IP 30

Illumination: 20 - 200 lm

Working life: 1 - 10 h

Number of rechargeable batteries contained: 1

Type of rechargeable battery: Lithium-ion

Overall length: 173 mm

Overall width: 17 mm

Technical description

Number of rechargeable batteries contained	1
Type of rechargeable battery	Lithium-ion
Illumination	20 - 200 lm
Weight	56 g
Overall width	17 mm
IP Index of Protection	IP 30
Overall length	173 mm
Working life	1 - 10 h
Power supply	Rechargeable battery-powered
Type of product	Flashlight