## HOLEX

# LED torch with rechargeable battery, Type: 170



### Order data

Order number	081364 170
GTIN	4062406942595
Item class	02A

### Description

#### Version:

Sturdy, rechargeable LED torch made of anodised aluminium. **The 2 settings** with additional **boost function** provide **outstanding light output** for all applications. The single-hand focussing enables quick and easy adjustment of the beam.

- $\cdot\,$  Charging and discharge monitoring by means of coloured LED in the switch.
- · Long running time with constant light output.
- · USB-C charging socket.
- Anti-roll protection.
- With focussable lamp head.

#### Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

#### Supplied with:

Supplied with USB-C charging cable and battery. With hand loop.

### Note:

For suitable replacement batteries see No. 081365 IP Index of Protection: IP 54 Torch function: Focus Illumination: 500 lm Illumination step 2: 200 lm Light current boost: 900 lm Working life: 2 h Lighting life stage 2: 4.5 h Illumination duration boost: 30 s

## **Technical description**

Power supply	Rechargeable battery-powered
Overall length	164 - 176 mm
Battery capacity	2.9 A·h
CRI value	>80
Illumination	500 lm
Working life	2 h
Weight	160 g
Lighting life stage 2	4.5 h
Type of rechargeable battery	Lithium-ion
Head Ø	32 mm
Number of rechargeable batteries contained	1
Replaceable battery	yes
Illumination duration boost	30 s
Torch function	Focus
Battery voltage	3.7 V
Light current boost	900 lm
Bulb	LED lamp
IP Index of Protection	IP 54
Illumination step 2	200 lm
Type of product	Flashlight

## Accessories

Replacement battery 18650

081365 18650