HOLEX

LED pen torch with rechargeable battery, Type: 120

Order data

Order number	081360 120
GTIN	4062406942557
Item class	02A

Description

Version:
Sturdy, rechargeable LED torch made of anodised aluminium. **The 2 settings** with additional **boost function** provide **outstanding light output** for all applications. The single-hand focussing enables quick and easy adjustment of the beam.
· **Charging and discharge monitoring by means of coloured LED in the switch.**
· **Long running time with constant light output.**
· **USB-C charging socket.**
· **Anti-roll protection.**
· **With focussable lamp head.**
Function:
IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.
Supplied with:
Supplied with USB-C charging cable and battery. With hand loop.
Note:
For suitable replacement batteries see No. 081365
IP Index of Protection: IP 54
Torch function: Focus
Illumination: 80 lm
Illumination step 2: 30 lm
Light current boost: 130 lm
Working life: 1 h
Lighting life stage 2: 3 h
Illumination duration boost: 30 s

Technical description

Type of rechargeable battery	Lithium-ion
Light current boost	130 lm
Illumination duration boost	30 s
Replaceable battery	yes
Head Ø	18 mm
Working life	1 h
Battery capacity	0.32 A·h
IP Index of Protection	IP 54
Lighting life stage 2	3 h
Power supply	Rechargeable battery-powered
Bulb	LED lamp
Weight	29.5 g
Overall length	112 - 120 mm
Battery voltage	3.7 V
Illumination	80 lm
Torch function	Focus
Number of rechargeable batteries contained	1
Illumination step 2	30 lm
CRI value	>80
Type of product	Flashlight

Accessories

Replacement battery 10440	081365 10440