

LED torch with rechargeable battery, Type: 150



Order data

Order number	081363 150
GTIN	4062406942588
Item class	02A

Description

Version:

Sturdy, rechargeable LED torch made of anodised aluminium. **The 2 settings** with additional **boost function** provide **outstanding light output** for all applications. The single-hand focussing enables quick and easy adjustment of the beam.

- · Charging and discharge monitoring by means of coloured LED in the switch.
- · Long running time with constant light output.
- USB-C charging socket.
- · Anti-roll protection.
- · With focussable lamp head.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

Supplied with USB-C charging cable and battery. With hand loop.

Note:

For suitable replacement batteries see No. 081365

IP Index of Protection: IP 54

Torch function: Focus
Illumination: 400 lm

Illumination step 2: 140 lm Light current boost: 700 lm

Working life: 1.5 h Lighting life stage 2: 5 h

Illumination duration boost: 30 s

Technical description



Illumination step 2	140 lm
IP Index of Protection	IP 54
Head ∅	28 mm
Overall length	144 - 154 mm
Power supply	Rechargeable battery-powered
Battery capacity	1.6 A·h
Replaceable battery	yes
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	1
Illumination	400 lm
Torch function	Focus
Lighting life stage 2	5 h
Battery voltage	3.7 V
CRI value	>80
Working life	1.5 h
Bulb	LED lamp
Illumination duration boost	30 s
Weight	95 g
Light current boost	700 lm
Type of product	Flashlight

Accessories

Replacement battery 16650 081365 16650