

LED pen torch with rechargeable battery, Type: 160



Order data

Order number	081361 160
GTIN	4062406942564
Item class	02A

Description

Version:

Sturdy, rechargeable LED torch made of anodised aluminium. **The 2 settings** with additional **boost function** provide **outstanding light output** for all applications. The single-hand focussing enables quick and easy adjustment of the beam.

- · Charging and discharge monitoring by means of coloured LED in the switch.
- · Long running time with constant light output.
- USB-C charging socket.
- · Anti-roll protection.
- · With focussable lamp head.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

Supplied with USB-C charging cable and battery. With practical pocket clip.

Note:

For suitable replacement batteries see No. 081365

IP Index of Protection: IP 54

Torch function: Focus Illumination: 150 lm Illumination step 2: 50 lm Light current boost: 250 lm

Working life: 1 h

Lighting life stage 2: 3 h

Illumination duration boost: 30 s

Technical description



Illumination step 2	50 lm
Light current boost	250 lm
Working life	1 h
Number of rechargeable batteries contained	1
Overall length	154 - 161 mm
Type of rechargeable battery	Lithium-ion
Head Ø	18 mm
Battery voltage	3.7 V
Weight	41 g
Illumination	150 lm
Battery capacity	0.6 A∙h
Bulb	LED lamp
IP Index of Protection	IP 54
Lighting life stage 2	3 h
Torch function	Focus
Replaceable battery	yes
CRI value	>80
Illumination duration boost	30 s
Type of product	Flashlight

Accessories

Replacement battery 10840 081365 10840