

LED torches with batteries, Type: 140mm



Order data

Order number	081505 140
GTIN	4045197488367
Item class	01A

Description

Version:

Long-life and very sturdy LED torch of anodised aluminium. **LED technology** with **outstanding lighting power**.

- · Tight beam with little scatter loss.
- High energy efficiency for long illumination time.
- · Illuminated ring, easy to find in the dark.
- · Splash-proof, protection class IP54.

Switch at rear.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

Including battery No. 081559 LR3.

Note:

For suitable batteries see No. 081551 ff.

IP Index of Protection: IP 54

Illumination: 35 lm Working life: 10 h

Number of batteries contained: 2

Battery type: Micro, AAA Overall length: 140 mm

Head Ø: 16 mm

Technical description

Number of batteries contained	2
-------------------------------	---

Battery type	Micro, AAA
Illumination	35 lm
Working life	10 h
Head Ø	16 mm
Weight	54 g
IP Index of Protection	IP 54
Overall length	140 mm
Power supply	Battery-powered
Type of product	Flashlight

Accessories

Alkaline-manganese batteries International size LR3	081551 LR3
Alkaline-manganese batteries International size LR3	081553 LR3
Alkaline-manganese batteries International size LR3	081561 LR3
Alkaline-manganese batteries International size LR3	081552 LR3
Battery holder Version 3AAA	081506 3AAA
Alkaline manganese battery set International size LR3	081555 LR3
Lithium-metal batteries International size LR3	081559 LR3
Alkaline-manganese batteries International size LR3	081554 LR3
Alkaline-manganese batteries International size LR3	081556 LR3