

**Tape measure with mm/inch graduations, Tape length: 3m****Order data**

Order number	462014 3
GTIN	4045197879684
Item class	42G

Description**Version:**

Plastic casing with removable belt clip. Automatic tape return and stop, with damping effect. Sliding end hook. Tape measure printed black/red on yellow.

Tape measure with mm/inch graduations (upper edge inch, lower edge mm).

Reversible reading: mm / inch

Standard: EG II

Tape width: 16 mm

Body length: 66 mm

Body width: 27 mm

Body height: 59 mm

Technical description

Tape width	16 mm
Body length	66 mm
Body width	27 mm
Body height	59 mm
Standard	EG II

Calibration	G1
Reversible reading	mm / inch
Type of product	Measuring tape

Services

Calibration Locking tape measure maximum length 5 m	016140 5
Labelling laser-etched Type	018940
DAkkS Calibration locking tape measure 5	026250 5
Calibration Tape measure maximum length 5 m	026240 5