



Wire stripping tool VDE insulated, Overall length: 160 mm



Order data

Order number	728761 160
GTIN	4045197888099
Item class	72B

Description

Version:

Offset jaws with V-shaped cutting edges (up to max. 5 mm external Ø). Laid-in joint with "no-play" action and opening spring. With adjustable screw for cross section adjustment.

Handles with multi-component covering, **insulated up to 1000 V to DIN EN 60900 / VDE 0682-201.**

Jaws bright finished.

Material:

Special tool steel, drop-forged and oil-hardened.

Technical description

overall length	160 mm
Standard	DIN EN 60900 / VDE 0682-201
Cutter form	Vee cutter
Handle	Multi-component covering
Material	Special tool steel
Surface	bright finish
with return spring	yes
with adjustable screw for cross section adjustment.	yes
Type of product	Cutting pliers

