

Garant**Open ended spanner / ratchet ring spanner reversible 15° offset, Width across flats: 17mm****Order data**

Order number	614820 17
GTIN	4045197218827
Item class	61B

Description**Version:**

Drop forged. Ring end with especially smooth-running reversible ring ratchet. Extremely small working arc of 5°.

Material:

Chrome vanadium steel, matt chrome-plated.

Spanner length L: 233 mm

Jaw width b: 36.6 mm

Jaw height h_1 : 7.9 mm

Ring thickness h_2 : 10.9 mm

Ring \varnothing D: 33.3 mm

Ratchet torque rating: 270 N·m

Technical description

Spanner length L	233 mm
Ratchet torque rating	270 N·m
Jaw width b	36.6 mm
Ring thickness h_2	10.9 mm
Ring \varnothing D	33.3 mm
Jaw height h_1	7.9 mm
Width across flats	17 mm
Width across flats	metric

Ring setting	15 °
No. of teeth	72
Working arc	5 °
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	matt chrome-plated
Type of product	Spanner