

Garant
Open ended spanner / ratchet ring spanner set, imperial, Width across flats: 1/2in

Order data

| | |
|--------------|---------------|
| Order number | 614825 1/2 |
| GTIN | 4045197331243 |
| Item class | 61B |

Description
Version:

Drop forged. Ring end with especially smooth–running reversible ring ratchet. Extremely small working arc of 5°.

Material:

Chrome vanadium steel, matt chrome-plated.

Spanner length L: 180 mm

Jaw width b: 27.1 mm

Jaw height h_1 : 6 mm

Ring thickness h_2 : 9.3 mm

Ring \varnothing D: 25.5 mm

Ratchet torque rating: 115 N·m

Technical description

| | |
|-----------------------|----------|
| Spanner length L | 180 mm |
| Ratchet torque rating | 115 N·m |
| Jaw height h_1 | 6 mm |
| Ring \varnothing D | 25.5 mm |
| Jaw width b | 27.1 mm |
| Ring thickness h_2 | 9.3 mm |
| Width across flats | 1/2 in |
| Width across flats | imperial |

| | |
|-----------------------|-----------------------|
| Ring setting | 0 ° |
| No. of teeth | 72 |
| Working arc | 5 ° |
| Manufacturing process | drop forged |
| Material | Chrome vanadium steel |
| Surface | matt chrome-plated |
| Type of product | Spanner |