HOLEX

Torch LED and UV with rechargeable battery, Type: UV-LED



Order data

Order number	081518 UV-LED
GTIN	4045197967251
Item class	02A

Description

Version:

Rechargeable anodized aluminium LED torch with battery, 3-stage LED, **switchable to UV light**, **90° rotating head** and magnetic base. Latest LED technology with outstanding lighting power.

$\cdot\,$ Rubber cover for the operating button.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

Supplied with USB-C charging cable. IP Index of Protection: IP 54 Illumination: 450 Im Illumination step 2: 300 Im Illumination step 3: 120 Im Working life: 2 - 8 h Wavelength of UV radiation: 395 nm Number of rechargeable batteries contained: 1

Technical description

Battery capacity	2.6 A·h
Illumination step 2	300 lm
IP Index of Protection	IP 54
Illumination	450 lm
Working life	2 - 8 h

Head Ø	29 mm
Wavelength of UV radiation	395 nm
Number of rechargeable batteries contained	1
Overall length	158 mm
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Illumination step 3	120 lm
Type of product	Flashlight