

Electronics side cutter, small head shape, FW, Overall length: 125mm



Order data

Order number	726170 125
GTIN	4045197976468
Item class	71B

Description

Version:

Precision machined with slim shape. Cutting edges induction hardened (62 - 64 HRC). Non-reflecting surface, matt shot-blasted with inlaid joint and countersunk screw. Double interchangeable springs for easy operation. **2-component** conductive grips. **Suitable for ESDs.** Cutting edges precision ground.

Material:

CNC-machined special tool steel for extremely accurate tolerances.

Cutting chamfer: fine bevel

Head width: 10 mm Cutter length: 10 mm

Cutting capacity copper wire up to Ø: 0.2 - 1.2 mm

Technical description

Cutting capacity copper wire up to \varnothing	0.2 - 1.2 mm
Head width	10 mm
Cutter length	10 mm
overall length	125 mm
electrostatic characteristic	EGB/ESD
Cutting chamfer	fine bevel
Product name attribute	FW

Type of product Cutting pliers