



Electrician's screwdriver for slot-head fully insulated, Blade width b: 3 mm



Order data

Order number	663301 3
GTIN	4062406059675
Item class	62F

Description

Version:

Handle and blade **fully insulated up to 1000 V to DIN EN 60900 / VDE 0682-201**.

Each of these screwdrivers is individually tested in a water bath for insulation breakdown under high voltage.

Multi-component power handle with grip zone optimised for torque and comfort. Blade of high-alloy tool steel. From size 5.5 the outside \varnothing of the insulation is the same as the tip width (helpful when working in narrow spaces).

Blades with taper tips, manufactured to the standard dimensions of slots on the screws. Fully insulated, the breakdown strength of the insulation is many times the minimum test voltage set by VDE. Each of these screwdrivers is individually tested in a water bath for insulation breakdown under high voltage.

Application:

For use at voltages up to 1000 V.

Optimum working life for electrician's screwdrivers is assured if screwdrivers always exactly match the standard screw slot size. (see tables part). Incorrect screwdriver size selection will cause damage to the screw head.

Tip thickness a: 0.5 mm

Blade length: 100 mm

overall length: 187 mm

Technical description

Tip thickness a	0.5 mm
Blade width b	3 mm
overall length	187 mm
Blade length	100 mm

Standard	DIN EN 60900 / VDE 0682-201
Drive profile	Slot-head screwdriver
Type of product	Screwdrivers