

ABP1614



Sample image

Order symbol: ABP1614

Product nbr: 8592181

Description: Painted Steel Back Panel

Remarks:

EAN: 6418074067913

EI. number:

- Finland:
- Denmark:
- Sweden:

Including:

Dimensions:	Height	Width	Depth
mm:	375	327	
inch:	14.8	12.9	

Materials:

Material:	Steel
Base colour:	
Cover colour:	
Gasket material:	

Temperatures:

Temperature °C (short term):
Temperature °C (continuous):
Temperature °F (short term):
Temperature °F (continuous):

Rating:

Ingress protection (EN 60529):	
Impact Resistance (EN 62262):	
Electrical insulation:	Not insulated
Halogen free (DIN/VDE 0472, Part 815):	0
UV resistance:	-
Flammability Rating:	
Glow Wire Test (IEC 695-2-1) °C:	C
NEMA Class	

Certificates: