## ARK14127CHSC





Sample image

Order symbol: ARK14127CHSC

Product nbr: 8561586

Description: PC Enclosure


Remarks: Hinged opaque screw cover. Base includes 1/2 and 3/4 inch knock-outs.

EAN: 6418074097620

## El. number:

Finland:Denmark:Sweden:

**Including:** Hinged screw cover. Base with 10-32 brass inserts, cover with formed in place PUR gasket, stainless hinge pin and 2 cover screws. Base includes 1/2 and 3/4 inch knock-outs. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.



Dimensions:	Height	Width	Depth
mm:	356	305	178

Accessories:

ABP1412 Painted Steel Back Panel (325 x 274)

12 7 inch: 14

**Materials:** 

Material: Polycarbonate

Base colour: RAL 7035 -light grey Cover colour: RAL 7035 -light grey

Gasket material: Polyurethane

**Temperatures:** 

Temperature °C (short term):: -40 ... 140 Temperature °C (continuous): -40 ... 80 Temperature °F (short term): -40 ... 250 Temperature °F (continuous): -40 ... 175

Aluminum Swing Panel (305 x 355.7 x 0) ASP1412 ASPHK14 Swing Panel Kit w/o Panel 12" Mounting Flange Set AMFL12 Dead Front Panel w/ screws ADFP1412  $(308 \times 357.5 \times 0)$ Aluminum Back Panel ALBP1412 (325 x 274) **PVC Back Panel** APBP1412 (325 x 274) Swing Panel Kit incl. Panel ASPK1412

Rating:

Ingress protection (EN 60529): IP66; IP67;

Impact Resistance (EN 62262): IK09;

Electrical insulation: Not insulated

Halogen free (DIN/VDE 0472,

Part 815):

UV resistance: **UL 508** Flammability Rating:

Glow Wire Test (IEC 695-2-1)

NEMA 4, 4X, 6, 6P, 12, 12K **NEMA Class** 

and 13

**UL 508** 

960 °C

1

## **Certificates:**

© Fibox Oy, Data subject to change without notice (printed: 19.07.2022)