



1 2D Views

2 Configuration settings

Configuration	
Part Number	HSM4-8-15-1
Description	Female To Female Standoff - White ; Nylon ; M4 ; Spacer Length 15.0 mm 0.591 in
Material Flammability Standard	UL94 V-2
Full Material	Nylon 6/6
Spacer Shape	Hexagonal
Maximum Operating Temperature (Seed)	185 °F
Internal Thread Length (Seed)	6.0 mm
Minimum Operating Temperature (Seed)	-40 °F
Spacer Length (Seed)	15.0 mm
Distance Across Flats (Seed)	8.0 mm
Compatible Thread Sizes	M4

Bill of Materials Data	
Manufacturer	Essentra Components
Description	Female To Female Standoff - White ; Nylon ; M4 ; Spacer Length 15.0 mm 0.591 in
Part Number	HSM4-8-15-1