

**Ethernet Cable, Cat6A Patch Cable, Strain Relief, UTP, 2.1336m, 7 ft, Blue**

**RoHS  
Compliant**

Stock No.: CAT6A-0033

## FEATURES

- Strain Relief
- UTP
- 26 AWG
- Stranded Copper




## Product Description

Cat6 Snagless Network Patch Cable offers universal connectivity to computers and network components, such as routers, switch boxes, network printers, network-attached storage (NAS) devices, VoIP phones, and PoE devices.

## General Specifications

Attribute	Value
Terminated/Unterminated	Terminated
Connector Type	RJ45
Cable Type	Ethernet
Length	2.1336m
Gauge	26 AWG
Conductor	Bare Copper
Shield/Unshielded	Unshielded
Voltage Rating	30V
1.0 - 750MHz Impedance ( $\Omega$ )	100 $\pm$ 15
Maximum Operating Frequency	750MHz
Operating & Storage Temp.	-40°C to 60°C   -40°F to 140°F
Installation Temp.	-20°C to 60°C   -4°F to 140°F
Jacket Color	Blue

## Product Drawing



Dimensions: Millimeters (Inches)

### Part Number Table

Part Number	Description
CAT6A-0013	Ethernet Cable, Cat6A Patch Cable, Strain Relief, UTP, 0.3048m, 1 ft, Blue
CAT6A-0023	Ethernet Cable, Cat6A Patch Cable, Strain Relief, UTP, 0.9144m, 3 ft, Blue
CAT6A-0033	Ethernet Cable, Cat6A Patch Cable, Strain Relief, UTP, 2.1336m, 7 ft, Blue
CAT6A-0043	Ethernet Cable, Cat6A Patch Cable, Strain Relief, UTP, 3.048m, 10 ft, Blue
CAT6A-0053	Ethernet Cable, Cat6A Patch Cable, Strain Relief, UTP, 4.2672m, 14 ft, Blue
CAT6A-0073	Ethernet Cable, Cat6A Patch Cable, Strain Relief, UTP, 7.62m, 25 ft, Blue
CAT6A-0153	Ethernet Cable, Cat6A Patch Cable, Strain Relief, UTP, 15.24m, 50 ft, Blue
CAT6A-0233	Ethernet Cable, Cat6A Patch Cable, Strain Relief, UTP, 22.86m, 75 ft, Blue
CAT6A-0303	Ethernet Cable, Cat6A Patch Cable, Strain Relief, UTP, 30.48m, 100 ft, Blue

Important Notice: This data sheet and its contents (the "Information") belong to the members of the EASE group of companies (the "Group") or are licensed to it. No license is granted for the use of it other than for information purposes in connection with the products to which it relates. No license of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate, but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. EASE is the registered trademark of Ease Electronics Co., Limited 2019.