Spherical sensor for pinless non-invasive testing

Features:

- Measure moisture content in wood and other building materials
- Audible indicator (with disable) increases as the moisture level gets higher
- · Low, Medium, High moisture level icons
- · Data Hold freezes measurement on screen
- · Self-calibration on power up
- · Auto power off after 20 seconds
- · Low battery indicator
- · Includes 9V battery

Applications:

- · Home Inspection
- · Water Damage Restoration
- Lumber Yards
- Painting
- Paper Mills
- · Textile and Clothing Manufacturing

Specifications

•	
Pinless Measurement Range	Wood: 0.1 to 99.9%
	Building Material: 0.1 to 99.9%
Resolution	0.1%
Measurement Depth	4" (102mm)
Visual Alert	Low, Medium, High icons
Icon Levels for Wood	Low: 0.1 to 16.9%
	Medium: 17 to 39.9%
	High: 40.0 to 99.9%
lcon Levels for Building Materials	Low: 0.1 to 16.9%
	Medium: 17.0 to 39.9%
	High: 40.0 to 99.9%
Audible Alert	Beeper increases in speed as moisture level goes up
Power	9V Battery
Dimensions	8.3 x 2.8 x 1.3" (210 x 70 x 33mm)
Weight	5.5oz (155g) (without battery)

Ordering Information:

MS300 Pinless Moisture Meter

