

ISSUE NUMBER

**ORIGINAL** 

ADD NOTE 3 & 4

P.M. AUG. 12/2023


CONTACT: BRASS, GOLD FLASH PLATING ALL OVER NICKEL UNDERPLATING

CONTACT RESISTANCE: 30mOHMS MAX. BEFORE TEST AND 60mOHMS MAX.

AFTER TEST POGO PIN WORKING STROKE.

SOLDERING OR MANUAL SOLDERING. OTHER FORMS OF SOLDERING SUCH AS WAVE SOLDER OR REFLOW SOLDER ARE NOT RECOMMENDED AND CAN POTENTIALLY CAUSE DEMAGNETIZATION OF MAGNET IN THE CONNECTOR

4- MATING WITH: 686F0321250110E, 686F0321350120E, 686F0321350124E, 686F0321250124E OR



RECOMMENDED P.C.B. LAYOUT (T:1.2mm) TOLERANCE UNSPECIFIED ±0.05mm

MAGNETIC SPRING LOADED CONNECTOR, 3 POS, MALE

THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.

11.60



EDAC INC TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC..AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

ACAD REFERENCE NO.: 685F0	)321351124E	UNIT: MM
DRAWN: J.L.	DATE: 8/12/2023	
CHECKED: R.S.M	DATE: 8/12/2023	}
SCALE: (IN CAD 1:1)	SHEET 1 OF	- 1
DRAWING NUMBER: 685E0321351124E		ISSUE

PART NUMBER: 685F0321351124E