TOLERANCE UNLESS OTHERWISE SPECIFIED .X ±0.15 .XX ±0.10 THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.




ISSUE NUMBER **ORIGINAL**

ADD NOTE 4 & 5

P.M.

AUG. 12/2023





SPECIFICATION:

1- MATERIAL:

CONTACT: BRASS GOLD FLASH PLATING ALL OVER NICKEL UNDERPLATING

HOUSING: PA46 BLACK

MAGNET: N52


2- ELECTRICAL:


RATED VOLTAGE (PER CONTACT): 12V RATED CURRENT (PER CONTACT): 2A

3- WORKING TEMPÈRATURE RANGÉ: -30~+85°C

4- RECOMMENDED SOLDERING PROCESS ARE SELECTIVE SOLDERING OR MANUAL SOLDERING. OTHER FORMS OF SOLDERING SUCH AS WAVE SOLDER OR REFLOW SOLDER ARE NOT RECOMMENDED AND CAN POTENTIALLY CAUSE DEMAGNETIZATION OF MAGNET IN THE CONNECTOR

5- MATING WITH: 685A1821220113Q





| MAGNETIC SPRING LOADED CONNECTOR, |
|-----------------------------------|
| 18POS, FEMALE |



1.00 ± 0.05

21.40

EDAC INC TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC..AND SHALL NOT BE REPRODUCED,OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

| | ACAD REFERENCE NO.: 686A1821F20111E | | UNIT: MM |
|--|-------------------------------------|-----------------|----------|
| | DRAWN: J.L. | DATE: 8/12/2023 | 3 |
| | CHECKED: R.S.M | DATE: 8/12/2023 | 3 |
| | SCALE: (IN CAD 1:1) | SHEET 1 OF | = 1 |
| | DDAMINO NUMBER 0000 1001500 1115 | | |

DRAWING NUMBER: 686A1821F20111E ISSUE 2 PART NUMBER: 686A1821F20111E

THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.