

TOLERANCE UNLESS OTHERWISE SPECIFIED .XX ±0.10

THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER **ORIGINAL**

ADD NOTE 4 & 5

P.M. AUG. 10/2023

REVISE NOTE 1 &

DELETE DIM 0.48, R3.60, R4.05 DELETE DIM 7.65, Ø1.50±0.05

AUG. 18/2023

SPECIFICATION:

1- MATERIAL:

CONTACT: BRASS, GOLD FLASH PLATING ALL OVER NICKEL UNDERPLATING INSULATION: PA46 + 30%GF, BLACK

MAGNET: N52


2- ELECTRICAL:

RATED VOLTAGE (PER CONTACT): 5V RATED CURRENT (PER CONTACT): 2A

3- WORKING TEMPERATURE RANGE: -30°C~+85°C

4- RECOMMENDED SOLDERING PROCESS ARE SELECTIVE SOLDERING OR MANUAL SOLDERING. OTHER FORMS OF SOLDERING SUCH AS WAVE SOLDER OR REFLOW SOLDER ARE NOT RECOMMENDED AND CAN POTENTIALLY CAUSE DEMAGNETIZATION OF MAGNET IN THE CONNECTOR

5- MATING WITH: 687C0222A000C00, 687C0222A001C00, 687C0222A001K00, 687C0222A000K00 OR 685C02212021C1E



MAGNETIC SPRING LOADED CONNECTOR, 1POS, FEMALE



EDAC INC TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC..AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

ACAD REFERENCE NO.: 68	6C02222030C1E UNIT: MM
DRAWN: J.L.	DATE: 8/21/2023
CHECKED: R.S.M	DATE: 8/21/2023
SCALE: (IN CAD 1:1)	SHEET 1 OF 1

DRAWING NUMBER: 686C02222030C1E ISSUE 3 PART NUMBER: 686C02222030C1E

THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.

COMPLIANT