
TOLERANCE UNLESS OTHERWISE SPECIFIED ±0.15 .XX ±0.10 THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER



ISSUE NUMBER (1) ORIGINAL ADD NOTE 6 & 7

P.M. AUG. 12/2023



**SPECIFICATIONS:** 

- **VOLTAGE RATING: 12V**
- 2. **CURRENT RATING: 2.0A MAX**
- 3. CONTACT RESISTANCE: 50mOHMS MAX
- **DURABILITY: 10000 CYCLES MIN** 4.
- 5. OPERATING TEMPERATURE: -30°C ~ +85°C
- RECOMMENDED SOLDERING PROCESS ARE SELECTIVE SOLDERING OR MANUAL SOLDERING. OTHER FORMS OF SOLDERING SUCH AS WAVE SOLDER OR REFLOW SOLDER ARE NOT RECOMMENDED AND CAN POTENTIALLY CAUSE DEMAGNETIZATION OF MAGNET IN THE CONNECTOR


MATING WITH: 685C0424350120E



.8

7.

5.4



4 - Ø 0.60 ± 0.02

3	MAGNET	N52, DIMENSION: 5.0*2.7*3.0MM, 200µ'' MIN NICKEL PLATING	1
2	HOUSING	PA46, 4 POS, BLACK COLOR	1
1	PIN	Ø1.3*8.0, BRASS, GOLD FLASH PLATING ALL OVER, 50-120µ" MIN NICKEL PLATING	4
ITEM	NAME	DESCRIPTION	QTY

SW REFERENCE NO .:

686 SERIES POGO CONNECTOR, 4 POS, SOCKET, VERTICAL



**EDAC INC** TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC., AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: J.L. DATE: MAY 16/2023 CHECKED: R.S.M. DATE: MAY 16/2023 SCALE: 3:1 SHEET 1 OF 1 DRAWING NUMBER: 686C0422250110E ISSUE 2 PART NUMBER: 686C0422250110E

686C0422250110E

UNIT: MM

9 4

> THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.