TOLERANCE UNLESS OTHERWISE SPECIFIED ±0.15 .XX ±0.10 THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.




ISSUE NUMBER (1) ORIGINAL ADD NOTE 4 & 5

P.M.

AUG. 12/2023







1- MATERIALS:

HOUSING: PA46, UL 94V-0, BLACK

CONTACT: BRASS, GOLD FLASH PLATING ALL OVER,

NICKEL UNDERPLATING

MAGNET: N52, NICKEL PLATING ALL OVER

PCB: FR4

2- ELECTRICAL:

VOLTAGE RATING: 12V CURRENT RATING: 2.0A MAX

CONTACT RESISTANCE: 30mOHMS MAX


3- MECHANICAL:

DURABILITY: 30000 CYCLES MIN


OPERATING TEMPERATURE: -40°C ~ +85°C

4- RECOMMENDED SOLDERING PROCESS ARE SELECTIVE SOLDERING OR MANUAL SOLDERING. OTHER FORMS OF SOLDERING SUCH AS WAVE SOLDER OR REFLOW SOLDER ARE NOT RECOMMENDED AND CAN POTENTIALLY CAUSE DEMAGNETIZATION OF MAGNET IN THE CONNECTOR

5- MATING WITH: 685E0322250110E



 8.4 ± 0.3



686 SERIES POGO CONNECTOR, 4 POS, SOCKET, RIGHT ANGLED



EDAC INC TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC., AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

	SW REFERENCE NO.:	686E0)321350120E		UNIT: MM	
	DRAWN: J.L.		DATE: MAY 16/2023			
	CHECKED: R.S.M.		DATE: 1	MAY 16	3/20)23
	SCALE: 3:1		SHEET 1 OF 1			
)	DRAWING NUMBER: 6	86E03	21350120E			ISSUE
;	PART NUMBER: 686E0321350120E				2	



THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.