

18.90

3 - Ø0.60

TOLERANCE UNLESS OTHERWISE SPECIFIED			
Y	+0 15		

.XX ±0.10

THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.




ISSUE NUMBER **ORIGINAL** 

ADD NOTE 3 & 4

P.M. AUG. 12/2023

4.00 2.50



RECOMMENDED PCB LAYOUT (T:1.2mm) TOLERANCE UNSPECIFIED ±0.05mm

SPECIFICATION:

1- MATERIAL:

CONTACT: BRASS GOLD FLASH PLATING ALL OVER NICKEL UNDERPLATING MAGNET: N52

HOUSING: PA9T, BLACK

2- ELECTRICAL:

RATED VOLTAGE (PER CONTACT): 5V

RATED CURRENT (PER CONTACT): 2A

INSULATION RESISTANCE: 100MEGAOHMS MINIMUM

DIELECTRIC WITHSTANDING VOLTAGE: 100V AT 60Hz

CONTACT RESISTANCE: 30mOHMS MAXIMUM BEFORE TEST AND

60mOHMS MAXIMUM

3- RECOMMENDED SOLDERING PROCESS ARE SELECTIVE SOLDERING OR MANUAL SOLDERING. OTHER FORMS OF SOLDERING SUCH AS WAVE SOLDER OR REFLOW SOLDER ARE NOT RECOMMENDED AND CAN POTENTIALLY CAUSE DEMAGNETIZATION OF MAGNET IN THE CONNECTOR


4- MATING WITH: 687F0321A51110E, 685F0321251110E, 685F0321351124E, 685F0321351120E 685F0321251124E OR 685F0321451110E



8

20 3

> THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.





1.80

EDAC INC TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC..AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

ACAD REFERENCE NO.: 686F0321350120E		UNIT: MM
DRAWN: J.L.	DATE: 8/12/2023	3
CHECKED: R.S.M	DATE: 8/12/2023	3
SCALE: (IN CAD 1:1)	SHEET 1 OF	= 1
DRAMINO NUMBER COSTOCO	100115	

DRAWING NUMBER: 686F0321350120E ISSUE PART NUMBER: 686F0321350120E