TOLERANCE UNLESS OTHERWISE SPECIFIED .X ±0.15

.XX ±0.10


THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.




ISSUE NUMBER **ORIGINAL** ADD NOTE 8


P.M.











SPECIFICATION:

1- MATERIAL:

CONTACT: BRASS, GOLD FLASH PLATING ALL OVER NICKEL UNDERPLATING

HOUSING: PA46, WHITE

MAGNET: N52

CABLE: TPE, GREY, OD: 2.5±0.10

2- ELECTRICAL:

VOLTAGE RATING (PER CONTACT): 5V CURRENT RATING (PER CONTACT): 1A

INSULATION RESISTANCE: 300V/DC 10MEGAOHMS (MIN.)

ON-RESLSTANCE: 30HMS MAXIMUM

100% BREAK/SHORT TEST

- 3- SWING TEST: LIFTING WEIGHT 200g, ±60 DEGREES, 30 TIMES/MIN, 2000 TIMES CONDUCTION OK.
- 4- SALT SPRAY TEST: 5% SALT SPRAY CONCENTRATION, TEMPERATURE 35°C, TEST TIME 48 HOURS, NO CORROSION.
- 5- WORKING STROKE & FORCE: PRESS STROKE 1.0mm (PER CONTACT) 50gf MAX.
- 6- LIFE TEST: PRESS STROKE 0.8mm, 10,000 CYCLES MIN.
- 7- OPERATING TEMPERATURE RANGE: -30°C~+85°C.

8- MATING WITH: 686B0822250210E

MAGNETIC SPRING LOADED CONNECTOR TO USB-A CABLE ASSEMBLY, 8POS, MALE

YOUR CONNECTION TO QUALITY & SERVICE

EDAC INC TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC..AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

ACAD REFERENCE NO.: 687B0812A512100				UNIT: MM	
DRAWN: J.L.		DATE:	8/12/	2023	
CHECKED: R.S.M		DATE:	8/12/	2023	
SCALE: (IN CAD 1:1)		SHEET	1	OF	1
DRAWING NUMBER: 607B0042A542400					ICCLIE

WIRING TABLE

RED

BLACK 4 GND

DRAWING NUMBER: 687B0812A512100 ISSUE PART NUMBER: 687B0812A512100



THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.