


THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.





ISSUE NUMBER ORIGINAL ADD NOTE 7

(2)

P.M. AUG. 13/2023







SPECIFICATION:

1- MATERIAL:

CONTACT: BRASS, GOLD FLASH PLATING ALL OVER NICKEL UNDERPLATING

HOUSING: PA9T, BLACK

MAGNET: N52

CABLE: TPE, BLACK, O.D.: 3.0, AWG 22

2- ELECTRICAL:

COMPLIANT

RATED VOLTAGE: 5V RATED CURRENT: 2A

INSULATION RESISTANCE: 300V/DC 10MEGAOHMS MIN.

ON-RESISTANCE: 2 OHMS MAX. 100% BREAK/SHORT TEST

- 3- SWING TEST: LIFTING WEIGHT 500g , ±60 DEGREES, 500 TIMES, 2000 TIMES CONDUCTION OK
- 4- RECOMMENDED WORKING STROKE & FORCE: STROKE 0.9mm (PER CONTACT) 40gf±20gf MAX.
- 5- MECHANICAL LIFE: 10,000 CYCLES MIN.
- 6- OPERATING TEMPERATURE RANGE: -30~+85°C.
- 7- MATING WITH: 686J0421251124E, 686J0421450124E OR 686J0421350124E

WIRING TABLE

RED VCC

<u>P2</u>

2

BLACK GND

MAGNETIC SPRING LOADED CONNECTOR, 4POS, MALE



EDAC INC TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC..AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

	ACAD REFERENCE NO.: 687J0421051110A		UNIT: MM
	DRAWN: J.L.	DATE: 8/15/2023	
	CHECKED: R.S.M	DATE: 8/15/2023	
	SCALE: (IN CAD 1:1)	SHEET 1 O	F 1
	DRAWING NUMBER: 687J0421051110A		ISSUE

687J0421051110A

PART NUMBER:

THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.