


58.6±0.5 12.8 Ø40.1 Ø42.0±0.5 1 11/16-18 UNEF THREAD M35 x 1.75 THREAD

REVISIONS REV ECO DESCRIPTION APPR DATE A1 RELEASE NEW DRAWING 19APR23 LYNCH TOMMY



NOTES: UNLESS OTHERWISE SPECIFIED

1. MATERIAL:

HOUSING: THERMOPLASTIC; BLACK SEAL: SILICONE RUBBER

- 2. MODIFICATIONS: SMALL THREADED ADAPTER (STA); STANDARD DIA. WIRE SEAL.
- 3. SPECIFICATIONS:
 - 3.1 OPERATING TEMPERATURE: -55°C TO +125°C.
 - 3.2 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.
 - 3.3 INSULATION RESISTANCE: 1000 MEGOHM MIN @ 25°C.
 - 3.4 MOISTURE RESISTANCE:


IP68(IM OF WATER FOR A PERIOD OF 24 HOURS, MATED CONDITION);

IP69K (MATED CONDITION)

- 3.5 MATING CYCLE DURABILITY: 100 CYCLES
- 3.6 RoHS COMPLIANT
- 4. MATING PART: AHDP06-24-18P*-XXX (*=SEAL TYPE, XXX=ALL MODIFICATIONS)
- 5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.


6 CONTACT SIZE AND WIRE RANGE:

| CONTACT | MIN. INSUL | MAX. INSUL | TYPICAL | CURRENT |
|---------|----------------------|----------------------|---------------------------|---------|
| SIZE | O.D. | O.D. | WIRE RANGE | RATING |
| 8 | 3.43 mm (.135in) | 5.59 mm (.220in) | 8-10 AWG (10.0-5.0mm²) | 80 AMPS |
| 12 | 2.46 mm (.097 in) | 4.01 mm (.158 in) | 10-14 AWG (6.0-2.0mm²) | 25 AMPS |
| 16 | 1.35 mm (.053 in) | 3.05 mm (.120 in) | 14-20 AWG (2.0-0.5mm²) | 13 AMPS |



RECOMMENDED PANEL THICKNESS:1.6 TO 4.7MM

- 7. RECEPTACLE IS SUPPLIED WITH DUST CAP.
- 8. CONDUIT ADAPTER ACCEPTS BACKSHELL (AHDPBS-24L015-005) CABLE Ø14.5 ~ Ø18.0.



ITEM

| | AHDP04-2 | 4-185K-51A | | | | | | |
|--------------------------------------------------------------|-----------------------|---------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------|-------------------------------|------|----------------------------|----|
| QUANTITY | PART N | NUMBER | DESCRIPTION | | | ITEM | | |
| | MATER | | | | | S LI | ST | |
| UNLESS OTHERWISE SPECIFIED SIGNATURES | | | S DAT | Te Amphanal | | | | |
| 1) All dimensions a 2) Tolerances are a 1 PL DEC ±0.30 | | DRAWN: LYNCH.PA | 19APR | Ampheno | | | mpnenoi | |
| 2 PL DEC 40.45 Apples 441 CHECKED: QUILINITALINI COARDON | | | | ne Systems - www.amphenol-sine.com | | | | |
| 3) Note reference | 3) Note reference = X | | | 44724 Morley Drive | | | | |
| MATERIAL SPECIFICA | TIONS: | APPROVAL: TOMMY.XIE | 20APR | 23 | | | Clinton Township, MI 48036 | |
| WEIGHT | · 61 0a | CUSTOMER: | ' | | | | RECEPTACLE, SOCKET, SIZE | |
| | | | THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION, NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL | | REDUCED SEAL, STA, DURAMATE A | | | |
| PROCESS SPECIFICATIONS: | | SHOWN HEREON ARE THE THE AMPHENOL CORPOR | | | В | C- | AHDP04-24-18SR-STA | A1 |
| NEXT ASS'Y: | | MANUFACTURING VARIAT | | | SCALE: N | ONE | DURAMATE SHEET 1 OF | 1 |

AUDD04 24 100D STA

A Series™ - Contact Size 8 Options (Works with: ATHD and DuraMate Series)

| Machined Contacts, Pins and Sockets | | | | | | |
|-------------------------------------|------------------------------------------------------|------|------|----------|------|--|
| Part Number | Description | Size | AWG | Туре | Amps | |
| AT60-204-08141 | Male Contact - Pin, Copper Alloy, Nickel-Plated | 8 | 8-10 | Machined | 60A | |
| AT62-203-08141 | Female Contact - Socket, Copper Alloy, Nickel-Plated | 8 | 8-10 | Machined | 60A | |
| AT60-204-08141-16 | Male Contact - Pin, Copper Alloy, Nickel-Plated | 8 | 6 | Machined | 60A | |
| AT62-203-08141-16 | Female Contact - Socket, Copper Alloy, Nickel-Plated | 8 | 6 | Machined | 60A | |

| | Tooling - Machined Contacts | | | | |
|-------------|-----------------------------------------------------------------------------------------------------------|--|--|--|--|
| Part Number | Description | | | | |
| WA23 | Heavy Duty Pneumatic Crimp Tool -Uses Universal Positioner Part No. WA23-101DA and Crimp Locator MFX-3961 | | | | |
| WA23-2 | Die Assembly -for CA-5E12 Heavy Duty Pneumatic Crimp Tool, Size 8 | | | | |
| WA23-3 | Die Assembly -for CA-5E12 Heavy Duty Pneumatic Crimp Tool, Size 6 | | | | |
| WA23-10 | Contact Locator, Size 6 and Size 8 | | | | |
| 96-978-22 | Crimper and Dies -for Size 10mm²-185mm² Wires | | | | |
| AT114008 | Contact Removal Tool, Plastic, Size 8, 8-10AWG | | | | |

A Series™ - Contact Size 12 Options (Works with: AHD-6, ATP, ATHD, DuraMate and PanelMate Series)

| Machined Contacts, Sockets & Pins | | | | | | |
|-----------------------------------|----------------------------------------|------|-------|----------|--|--|
| Part Number | Description | Size | AWG | Туре | | |
| *AT60-204-12141-10 | Male Contact - Pin, Nickel-plated | 12 | 10-12 | Machined | | |
| *AT62-203-12141-10 | Female Contact - Socket, Nickel-plated | 12 | 10-12 | Machined | | |
| AT60-220-1231 | Male Contact - Pin, Gold-plated | 12 | 12-14 | Machined | | |
| AT62-210-1231 | Female Contact - Socket, Gold-plated | 12 | 12-14 | Machined | | |
| AT60-204-12141 | Male Contact - Pin, Nickel-plated | 12 | 12-14 | Machined | | |
| AT62-203-12141 | Female Contact - Socket, Nickel-plated | 12 | 12-14 | Machined | | |

^{*}Works with ATP Series only

| | DiagnosticGrade™ Machined Contacts, Sockets & Pins • Smaller AWG for Diagnostic Applications • Gold-plated • Increased Mating Cycles • Cost-effective | | | | | | | |
|---|-------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------|------|-----|----------|--|--|--|
| | Part Number | Description | Size | AWG | Туре | | | |
| Γ | 65-54749 | Male Contact - DiagnosticGrade™, Pin, Gold-plated | 12 | 20 | Machined | | | |
| | AT62-210-1231-1820 | Female Contact - DiagnosticGrade™, Socket, Gold-plated | 12 | 20 | Machined | | | |

| Tooling - Machined Contacts | | | | | |
|-----------------------------|--------------------------------------------------------------------|--|--|--|--|
| Part Number | Description | | | | |
| AUTK-12 | Hand Crimp Tool, Size 12 | | | | |
| AUTK-100 | Universal Heavy Duty Contact Crimping Tool Kit, Size 12/16/20 | | | | |
| CA-5D12 | Universal Hand Crimp Tool, Size 12/16/20 | | | | |
| CA-5E12 | Pneumatic Crimp Tool, Size 12/16/20 | | | | |
| M300-25A | Hand Crimp Tool used with Crimp Locator MFX-3966, Size 12, 10AWG | | | | |
| MFX-3966 | Contact Locator used with Hand Crimp Tool M300-25A, Size 12, 10AWG | | | | |

| Contact Removal Tools (For both Machined or Stamped & Formed Contacts) | | | | | |
|------------------------------------------------------------------------|----------------------------------------|--|--|--|--|
| Part Number | Description | | | | |
| ATRT-100 | Contact and Wedgelock Extraction Tool | | | | |
| AT11-337-1205 | Contact Removal Tool, Plastic, Size 12 | | | | |

| Sealing Plugs (For both Machined or Stamped & Formed Contacts) | | | | | |
|----------------------------------------------------------------|------------------------------|--|--|--|--|
| Part Number | Description | | | | |
| A114017 | Sealing Plug, Size 12, White | | | | |

| Stamped & Formed Contacts, Sockets & Pins | | | | | | | |
|-------------------------------------------|----------------------------------------|------|-------|------------------|--|--|--|
| Part Number | Description | Size | AWG | Туре | | | |
| AT60-12-0244 | Male Contact - Pin, Gold-plated | 12 | 10-12 | Stamped & Formed | | | |
| AT62-12-0244 | Female Contact - Socket, Gold-plated | 12 | 10-12 | Stamped & Formed | | | |
| AT60-12-0222 | Male Contact - Pin, Nickel-plated | 12 | 10-12 | Stamped & Formed | | | |
| AT62-12-0222 | Female Contact - Socket, Nickel-plated | 12 | 10-12 | Stamped & Formed | | | |
| AT60-12-0144 | Male Contact - Pin, Gold-plated | 12 | 12-14 | Stamped & Formed | | | |
| AT62-12-0144 | Female Contact - Socket, Gold-plated | 12 | 12-14 | Stamped & Formed | | | |
| AT60-12-0166 | Male Contact - Pin, Nickel-plated | 12 | 12-14 | Stamped & Formed | | | |
| AT62-12-0166 | Female Contact - Socket, Nickel-plated | 12 | 12-14 | Stamped & Formed | | | |

| Tooling - Stamped & Formed Contacts | | | | | |
|-------------------------------------|---------------------------------------------|--|--|--|--|
| Part Number | Description | | | | |
| MFX-3973 | Crimp Die - Size 12 | | | | |
| MFX-3985 | Crimp Die - Svize 12, 10-12AWG -02XX Series | | | | |
| ATT-12-00 | Hand Crimp Tool - Size 12, 12AWG | | | | |
| ATT-12-01 | Hand Crimp Tool - Size 12, 10AWG | | | | |

A Series™ - Contact Size 16 Options (Works with: AT, ATV, AHD-9, ARC, DuraMate and PanelMate Series)

| Machined Contacts, Sockets & Pins | | | | | | |
|-----------------------------------|----------------------------------------|------|-------|----------|--|--|
| Part Number | Description | Size | AWG | Туре | | |
| AT60-215-1631 | Male Contact - Pin, Gold-plated | 16 | 14 | Machined | | |
| AT62-209-1631 | Female Contact - Socket, Gold-plated | 16 | 14 | Machined | | |
| AT60-215-16141 | Male Contact - Pin, Nickel-plated | 16 | 14 | Machined | | |
| AT62-209-16141 | Female Contact - Socket, Nickel-plated | 16 | 14 | Machined | | |
| AT60-202-1631 | Male Contact - Pin, Gold-plated | 16 | 16-20 | Machined | | |
| AT62-201-1631 | Female Contact - Socket, Gold-plated | 16 | 16-20 | Machined | | |
| AT60-202-16141 | Male Contact - Pin, Nickel-plated | 16 | 16-20 | Machined | | |
| AT62-201-16141 | Female Contact - Socket, Nickel-plated | 16 | 16-20 | Machined | | |
| AT60-202-1631-22 | Male Contact - Pin, Gold-plated | 16 | 22-24 | Machined | | |
| AT62-201-1631-22 | Female Contact - Socket, Gold-plated | 16 | 22-24 | Machined | | |
| AT60-202-16141-22 | Male Contact - Pin, Nickel-plated | 16 | 22-24 | Machined | | |
| AT62-201-16141-22 | Female Contact - Socket, Nickel-plated | 16 | 22-24 | Machined | | |

| Tooling - Machined Contacts | | | |
|-----------------------------|---------------------------------------------------------------|--|--|
| Part Number | Description | | |
| AUTK-16 | Hand Crimp Tool, Size 16 | | |
| AUTK-100 | Universal Heavy Duty Contact Crimping Tool Kit, Size 12/16/20 | | |
| CA-5D12 | Universal Hand Crimp Tool, Size 12/16/20 | | |
| CA-5E12 | Pneumatic Crimp Tool, Size 12/16/20 | | |

| Contact Removal Tools (For both Machined or Stamped & Formed Contacts) | | | | |
|------------------------------------------------------------------------|----------------------------------------|--|--|--|
| Part Number | Description | | | |
| ATRT-100 | Contact and Wedgelock Extraction Tool | | | |
| AT11-310-1605 | Contact Removal Tool, Plastic, Size 16 | | | |

| Sealing Plugs (For both Machined or Stamped & Formed Contacts) | | | | |
|----------------------------------------------------------------|-------------------------------------------------|--|--|--|
| Part Number | Description | | | |
| A114017 | Sealing Plug, Size 16, White | | | |
| A114017-SR | Sealing Plug, Size 16, SR01 Series, Black | | | |
| AT13-217-1605 | Locking Sealing Plug, Size 16, Grey | | | |
| AT13-217-1605-SR | Locking Sealing Plug, Size 16, SR01 Series, Red | | | |

| Stamped & Formed Contacts, Sockets & Pins | | | | | | |
|-------------------------------------------|----------------------------------------|------|-------|------------------|--|--|
| Part Number | Description | Size | AWG | Туре | | |
| AT60-14-0122 | Male Contact - Pin, Nickel-plated | 16 | 14-18 | Stamped & Formed | | |
| AT62-14-0122 | Female Contact - Socket, Nickel-plated | 16 | 14-18 | Stamped & Formed | | |
| AT60-14-0144 | Male Contact - Pin, Gold-plated | 16 | 14-18 | Stamped & Formed | | |
| AT62-14-0144 | Female Contact - Socket, Gold-plated | 16 | 14-18 | Stamped & Formed | | |
| AT60-16-0122 | Male Contact - Pin, Nickel-plated | 16 | 16-18 | Stamped & Formed | | |
| AT62-16-0122 | Female Contact - Socket, Nickel-plated | 16 | 16-18 | Stamped & Formed | | |
| AT60-16-0144 | Male Contact - Pin, Gold-plated | 16 | 16-18 | Stamped & Formed | | |
| AT62-16-0144 | Female Contact - Socket, Gold-plated | 16 | 16-18 | Stamped & Formed | | |
| AT60-16-0622 | Male Contact - Pin, Nickel-plated | 16 | 16-20 | Stamped & Formed | | |
| AT62-16-0622 | Female Contact - Socket, Nickel-plated | 16 | 16-20 | Stamped & Formed | | |
| AT60-16-0644 | Male Contact - Pin, Gold-plated | 16 | 16-20 | Stamped & Formed | | |
| AT62-16-0644 | Female Contact - Socket, Gold-plated | 16 | 16-20 | Stamped & Formed | | |
| AT60-16-0677 | Male Contact - Pin, Tin-plated | 16 | 16-20 | Stamped & Formed | | |
| AT62-16-0677 | Female Contact - Socket, Tin-plated | 16 | 16-20 | Stamped & Formed | | |
| AT60-16-0822 | Male Contact - Pin, Nickel-plated | 16 | 20-22 | Stamped & Formed | | |
| AT62-16-0822 | Female Contact - Socket, Nickel-plated | 16 | 20-22 | Stamped & Formed | | |
| AT60-16-0844 | Male Contact - Pin, Gold-plated | 16 | 20-22 | Stamped & Formed | | |
| AT62-16-0844 | Female Contact - Socket, Gold-plated | 16 | 20-22 | Stamped & Formed | | |

| Tooling - Stamped & Formed Contacts | | |
|-------------------------------------|-------------------------------------|--|
| MFX-3950 | Crimp Die - Size 16, 18-20AWG | |
| MFX-3953 | Crimp Die - Size 16, 16-18AWG | |
| MFX-3975 | Crimp Die - Size 16, 14-16AWG | |
| MFX-3990 | Crimp Die - Size 16, 20-22AWG | |
| ATT-16-00 | Hand Crimp Tool - Size 16, 14-16AWG | |
| ATT-16-01 | Hand Crimp Tool - Size 16, 18-20AWG | |
| ATT-1612-03 | Hand Crimp Tool - Size 16, 20-22AWG | |