
	REVISIONS							
	REV	ECO	DESCRIPTION	DATE	BY	APPR		
Ī	A1	-	RELEASE NEW DRAWING	23/MAY/23	MILO	TOMMY		



NOTES: UNLESS OTHERWISE SPECIFIED

MATERIAL:

HOUSING: THERMOPLASTIC; BLACK SEAL: SILICONE RUBBER

2. MODIFICATIONS: SMALL THREADED ADAPTER(STA); REDUCED DIA. WIRE SEAL;

3. SPECIFICATIONS:

- 3.1 OPERATING TEMPERATURE: -55°C TO +125°C.
- 3.2 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.
- 3.3 INSULATION RESISTANCE: 1000 MEGOHM MIN @ 25°C.
- 3.4 MOISTURE RESISTANCE:

IP68(IM OF WATER FOR A PERIOD OF 24 HOURS, MATED CONDITION);


IP69K(MATED CONDITION)

- 3.5 MATING CYCLE DURABILITY: 100 CYCLES
- 3.6 RoHS COMPLIANT
- 4. MATING PART: AHDP02-24-14S*-XXX & AHDP04-24-14S*-XXX (* = SEAL TYPE, XXX = ALL MODIFICATIONS)
- 5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.

6 CONTACT SIZE AND WIRE RANGE:

CONTACT SIZE	MIN. INSUL O.D.	MAX. INSUL O.D.	TYPICAL WIRE RANGE	CURRENT RATING
4	6.63 mm (.261 in)	7.41 mm (.292 in)	6 AWG (16.0-13.0mm²)	100 AMPS
12	2.46 mm (.135 in)	4.01 mm (.158 in)	10-14 AWG (6.0-2.0mm²)	25 AMPS
16	1.35 mm (.053 in)	3.05 mm (.120 in)	14-20 AWG (2.0-0.5mm²)	13 AMPS

 CONDUIT ADAPTER ACCEPTS BACKSHELL (AHDPBS-24L015-005) CABLE Ø14.5 ~ Ø18.0.



SMALL THREADED ADAPTER -BLUE

	AHDP06-2	4-14PR-STA		REF:HDP26-24-14PE-L015			
QUANTITY	PART N	IUMBER	DESCRIPTION		DESCRIPTION	ITEM	
		MA	TI	ERI	ALS LIST		
UNLESS OTHER		SIGNATUR	RES	DATE	Amphonol		
All dimensions a Tolerances are a PL DEC ±0.30		DRAWN: MILO.DO	NG	23/MAY/23	Amphenol		
2 PL DEC ±0.15 3 PL DEC ±0.08	Angles ±1°	CHECKED: SULLENZH	IANG	24/MAY/23	Sine Systems - www.amphenol-sine.com	_	
3) Note reference = X		ENGINEER:			44724 Morley Drive		
MATERIAL SPECIFICA	TIONS:	APPROVAL: TOMMY	Œ	25/MAY/23	Clinton Township, MI 48036		
		CUSTOMER:			14POS,PLUG,PIN,24SZ,		
WEIGH	T: 63.1	THIS DRAWING IS SUPP			REDUCED SEAL, STA, DURAMATE AHD		
PROCESS SPECIFICATIONS:		INFORMATION ONLY. DE SPECIFICATIONS AND P SHOWN HEREON ARE T THE AMPHENOL CORPO OF REPRODUCTION ARE DIMENSIONS ARE SUBJ	ERFORI HE PRO RATION E IMPLIE	MANCE DATA PERTY OF I. NO RIGHTS ED. ALL	ATA SIZE TYPE DWG NO:		
NEXT ASS'Y:		MANUFACTURING VARI			SCALE: NONE DURAMATE SHEET 1 OF	1	

A Series™ - Contact Size 4 Options (Works with: ATHD and DuraMate Series)

Machined Contacts, Pins and Sockets							
Part Number	Description	Size	AWG	Туре	Amps		
AT60-203-04141-4	Male Contact - Pin, Copper Alloy, Nickel-Plated	4	4	Machined	100A		
AT60-204-0490	Male Contact - Pin, Copper Alloy, Nickel-Plated	4	6	Machined	100A		
AT62-203-04141-4	Female Contact - Socket, Copper Alloy, Nickel-Plated	4	4	Machined	100A		
AT62-203-04141	Female Contact - Socket, Copper Alloy, Nickel-Plated	4	6	Machined	100A		

	Tooling - Machined Contacts						
Part Number	Description						
WA23 Heavy Duty Pneumatic Crimp Tool -Uses Universal Positioner Part No. WA23-101DA and Crimp Locator MFX-3961							
WA23-138DA Die Assembly -for Heavy Duty Pneumatic Crimp Tool, Size 4							
WA23-11	Contact Locator, Size 4						
96-978-22	Crimper and Dies -for Size 10mm²-185mm² Wires						
AT11-027-0405 Contact Removal Tool, Plastic, Size 4, 4AWG							

A Series™ - Contact Size 12 Options (Works with: AHD-6, ATP, ATHD, DuraMate and PanelMate Series)

Machined Contacts, Sockets & Pins							
Part Number	Description	Size	AWG	Туре			
*AT60-204-12141-10	Male Contact - Pin, Nickel-plated	12	10-12	Machined			
*AT62-203-12141-10	Female Contact - Socket, Nickel-plated	12	10-12	Machined			
AT60-220-1231	Male Contact - Pin, Gold-plated	12	12-14	Machined			
AT62-210-1231	Female Contact - Socket, Gold-plated	12	12-14	Machined			
AT60-204-12141	Male Contact - Pin, Nickel-plated	12	12-14	Machined			
AT62-203-12141	Female Contact - Socket, Nickel-plated	12	12-14	Machined			

^{*}Works with ATP Series only

	DiagnosticGrade™ Machined Contacts, Sockets & Pins • Smaller AWG for Diagnostic Applications • Gold-plated • Increased Mating Cycles • Cost-effective								
	Part Number	Description	Size	AWG	Туре				
Γ	65-54749	Male Contact - DiagnosticGrade™, Pin, Gold-plated	12	20	Machined				
	AT62-210-1231-1820	Female Contact - DiagnosticGrade™, Socket, Gold-plated	12	20	Machined				

	Tooling - Machined Contacts							
Part Number	Description							
AUTK-12	Hand Crimp Tool, Size 12							
AUTK-100 Universal Heavy Duty Contact Crimping Tool Kit, Size 12/16/20								
CA-5D12 Universal Hand Crimp Tool, Size 12/16/20								
CA-5E12	Pneumatic Crimp Tool, Size 12/16/20							
M300-25A	Hand Crimp Tool used with Crimp Locator MFX-3966, Size 12, 10AWG							
MFX-3966	MFX-3966 Contact Locator used with Hand Crimp Tool M300-25A, Size 12, 10AWG							

Contact Removal Tools (For both Machined or Stamped & Formed Contacts)						
Part Number Description						
ATRT-100	Contact and Wedgelock Extraction Tool					
AT11-337-1205 Contact Removal Tool, Plastic, Size 12						

Sealing Plugs (For both Machined or Stamped & Formed Contacts)					
Part Number	Description				
A114017	Sealing Plug, Size 12, White				

Stamped & Formed Contacts, Sockets & Pins							
Part Number	Description	Size	AWG	Туре			
AT60-12-0244	Male Contact - Pin, Gold-plated	12	10-12	Stamped & Formed			
AT62-12-0244	Female Contact - Socket, Gold-plated	12	10-12	Stamped & Formed			
AT60-12-0222	Male Contact - Pin, Nickel-plated	12	10-12	Stamped & Formed			
AT62-12-0222	Female Contact - Socket, Nickel-plated	12	10-12	Stamped & Formed			
AT60-12-0144	Male Contact - Pin, Gold-plated	12	12-14	Stamped & Formed			
AT62-12-0144	Female Contact - Socket, Gold-plated	12	12-14	Stamped & Formed			
AT60-12-0166	Male Contact - Pin, Nickel-plated	12	12-14	Stamped & Formed			
AT62-12-0166	Female Contact - Socket, Nickel-plated	12	12-14	Stamped & Formed			

	Tooling - Stamped & Formed Contacts						
Part Number	Description						
MFX-3973	Crimp Die - Size 12						
MFX-3985	Crimp Die - Svize 12, 10-12AWG -02XX Series						
ATT-12-00	Hand Crimp Tool - Size 12, 12AWG						
ATT-12-01	Hand Crimp Tool - Size 12, 10AWG						

A Series™ - Contact Size 16 Options (Works with: AT, ATV, AHD-9, ARC, DuraMate and PanelMate Series)

	Machined Contacts, Sockets & Pins				
Part Number	Description	Size	AWG	Туре	
AT60-215-1631	Male Contact - Pin, Gold-plated	16	14	Machined	
AT62-209-1631	Female Contact - Socket, Gold-plated	16	14	Machined	
AT60-215-16141	Male Contact - Pin, Nickel-plated	16	14	Machined	
AT62-209-16141	Female Contact - Socket, Nickel-plated	16	14	Machined	
AT60-202-1631	Male Contact - Pin, Gold-plated	16	16-20	Machined	
AT62-201-1631	Female Contact - Socket, Gold-plated	16	16-20	Machined	
AT60-202-16141	Male Contact - Pin, Nickel-plated	16	16-20	Machined	
AT62-201-16141	Female Contact - Socket, Nickel-plated	16	16-20	Machined	
AT60-202-1631-22	Male Contact - Pin, Gold-plated	16	22-24	Machined	
AT62-201-1631-22	Female Contact - Socket, Gold-plated	16	22-24	Machined	
AT60-202-16141-22	Male Contact - Pin, Nickel-plated	16	22-24	Machined	
AT62-201-16141-22	Female Contact - Socket, Nickel-plated	16	22-24	Machined	

	Tooling - Machined Contacts		
Part Number	Description		
AUTK-16	Hand Crimp Tool, Size 16		
AUTK-100	Universal Heavy Duty Contact Crimping Tool Kit, Size 12/16/20		
CA-5D12	Universal Hand Crimp Tool, Size 12/16/20		
CA-5E12	Pneumatic Crimp Tool, Size 12/16/20		

Contact Removal Tools (For both Machined or Stamped & Formed Contacts)		
Part Number	Description	
ATRT-100	Contact and Wedgelock Extraction Tool	
AT11-310-1605	Contact Removal Tool, Plastic, Size 16	

Sealing Plugs (For both Machined or Stamped & Formed Contacts)		
Part Number	Description	
A114017	Sealing Plug, Size 16, White	
A114017-SR	Sealing Plug, Size 16, SR01 Series, Black	
AT13-217-1605	Locking Sealing Plug, Size 16, Grey	
AT13-217-1605-SR	Locking Sealing Plug, Size 16, SR01 Series, Red	

Stamped & Formed Contacts, Sockets & Pins				
Part Number	Description	Size	AWG	Туре
AT60-14-0122	Male Contact - Pin, Nickel-plated	16	14-18	Stamped & Formed
AT62-14-0122	Female Contact - Socket, Nickel-plated	16	14-18	Stamped & Formed
AT60-14-0144	Male Contact - Pin, Gold-plated	16	14-18	Stamped & Formed
AT62-14-0144	Female Contact - Socket, Gold-plated	16	14-18	Stamped & Formed
AT60-16-0122	Male Contact - Pin, Nickel-plated	16	16-18	Stamped & Formed
AT62-16-0122	Female Contact - Socket, Nickel-plated	16	16-18	Stamped & Formed
AT60-16-0144	Male Contact - Pin, Gold-plated	16	16-18	Stamped & Formed
AT62-16-0144	Female Contact - Socket, Gold-plated	16	16-18	Stamped & Formed
AT60-16-0622	Male Contact - Pin, Nickel-plated	16	16-20	Stamped & Formed
AT62-16-0622	Female Contact - Socket, Nickel-plated	16	16-20	Stamped & Formed
AT60-16-0644	Male Contact - Pin, Gold-plated	16	16-20	Stamped & Formed
AT62-16-0644	Female Contact - Socket, Gold-plated	16	16-20	Stamped & Formed
AT60-16-0677	Male Contact - Pin, Tin-plated	16	16-20	Stamped & Formed
AT62-16-0677	Female Contact - Socket, Tin-plated	16	16-20	Stamped & Formed
AT60-16-0822	Male Contact - Pin, Nickel-plated	16	20-22	Stamped & Formed
AT62-16-0822	Female Contact - Socket, Nickel-plated	16	20-22	Stamped & Formed
AT60-16-0844	Male Contact - Pin, Gold-plated	16	20-22	Stamped & Formed
AT62-16-0844	Female Contact - Socket, Gold-plated	16	20-22	Stamped & Formed

Tooling - Stamped & Formed Contacts		
MFX-3950	Crimp Die - Size 16, 18-20AWG	
MFX-3953	Crimp Die - Size 16, 16-18AWG	
MFX-3975	Crimp Die - Size 16, 14-16AWG	
MFX-3990	Crimp Die - Size 16, 20-22AWG	
ATT-16-00	Hand Crimp Tool - Size 16, 14-16AWG	
ATT-16-01	Hand Crimp Tool - Size 16, 18-20AWG	
ATT-1612-03	Hand Crimp Tool - Size 16, 20-22AWG	