

Sample Kit P/N: CC060300000SB000 [CC 0603 series]



No.	Part NO.	Size	TC	Cap.	Volt.	Tol	Qty	No.	Part NO.	Size	TC	Cap.	Volt.	Tol	Qty
1	CC0603JRNPO9BN100	0603	NPO	10pF	50V	±5%	40	26	CC0603KRX7R8BB223	0603	X7R	22nF	25V	±10%	40
2	CC0603JRNPO9BN120	0603	NPO	12pF	50V	±5%	40	27	CC0603KRX7R8BB473	0603	X7R	47nF	25V	±10%	40
3	CC0603JRNPO9BN150	0603	NPO	15pF	50V	±5%	40	28	CC0603KRX7R8BB224	0603	X7R	220nF	25V	±10%	40
4	CC0603JRNPO9BN180	0603	NPO	18pF	50V	±5%	40	29	CC0603KRX7R8BB474	0603	X7R	470nF	25V	±10%	40
5	CC0603JRNPO9BN200	0603	NPO	20pF	50V	±5%	40	30	CC0603KRX7R9BB101	0603	X7R	100pF	50V	±10%	40
6	CC0603JRNPO9BN220	0603	NPO	22pF	50V	±5%	40	31	CC0603KRX7R9BB151	0603	X7R	150pF	50V	±10%	40
7	CC0603JRNPO9BN270	0603	NPO	27pF	50V	±5%	40	32	CC0603KRX7R9BB221	0603	X7R	220pF	50V	±10%	40
8	CC0603JRNPO9BN300	0603	NPO	30pF	50V	±5%	40	33	CC0603KRX7R9BB331	0603	X7R	330pF	50V	±10%	40
9	CC0603JRNPO9BN330	0603	NPO	33pF	50V	±5%	40	34	CC0603KRX7R9BB471	0603	X7R	470pF	50V	±10%	40
10	CC0603JRNPO9BN470	0603	NPO	47pF	50V	±5%	40	35	CC0603KRX7R9BB681	0603	X7R	680pF	50V	±10%	40
11	CC0603JRNPO9BN560	0603	NPO	56pF	50V	±5%	40	36	CC0603KRX7R9BB102	0603	X7R	1nF	50V	±10%	40
12	CC0603JRNPO9BN680	0603	NPO	68pF	50V	±5%	40	37	CC0603KRX7R9BB152	0603	X7R	1.5nF	50V	±10%	40
13	CC0603JRNPO9BN101	0603	NPO	100pF	50V	±5%	40	38	CC0603KRX7R9BB222	0603	X7R	2.2nF	50V	±10%	40
14	CC0603JRNPO9BN151	0603	NPO	150pF	50V	±5%	40	39	CC0603KRX7R9BB332	0603	X7R	3.3nF	50V	±10%	40
15	CC0603JRNPO9BN221	0603	NPO	220pF	50V	±5%	40	40	CC0603KRX7R9BB472	0603	X7R	4.7nF	50V	±10%	40
16	CC0603JRNPO9BN331	0603	NPO	330pF	50V	±5%	40	41	CC0603KRX7R9BB682	0603	X7R	6.8nF	50V	±10%	40
17	CC0603JRNPO9BN471	0603	NPO	470pF	50V	±5%	40	42	CC0603KRX7R9BB103	0603	X7R	10nF	50V	±10%	40
18	CC0603JRNPO9BN561	0603	NPO	560pF	50V	±5%	40	43	CC0603KRX7R9BB153	0603	X7R	15nF	50V	±10%	40
19	CC0603JRNPO9BN681	0603	NPO	680pF	50V	±5%	40	44	CC0603KRX7R9BB223	0603	X7R	22nF	50V	±10%	40
20	CC0603JRNPO9BN102	0603	NPO	1nF	50V	±5%	40	45	CC0603KRX7R9BB333	0603	X7R	33nF	50V	±10%	40
21	CC0603KRX7R6BB224	0603	X7R	220nF	10V	±10%	40	46	CC0603KRX7R9BB473	0603	X7R	47nF	50V	±10%	40
22	CC0603KRX7R6BB474	0603	X7R	470nF	10V	±10%	40	47	CC0603KRX7R9BB683	0603	X7R	68nF	50V	±10%	40
23	CC0603KRX7R7BB224	0603	X7R	220nF	16V	±10%	40	48	CC0603KRX7R9BB104	0603	X7R	100nF	50V	±10%	40
24	CC0603KRX7R7BB334	0603	X7R	330nF	16V	±10%	40	49	CC0603KRX7R9BB224	0603	X7R	220nF	50V	±10%	40
25	CC0603KRX7R7BB474	0603	X7R	470nF	16V	±10%	40	50	CC0603KRX5R8BB474	0603	X5R	470nF	25V	±10%	40