

**QL 3 SAKH10****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Similar to illustration

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

**General ordering data**

|            |   |
|------------|---|
| Version    | SAK Series, Cross-connector, Cross-connector,<br>Number of poles: 3 |
| Order No.  | <a href="#">0131500000</a>  |
| Type       | QL 3 SAKH10   |
| GTIN (EAN) | 4008190056490   |
| Qty.       | 50 pc(s).   |

Creation date January 9, 2024 4:24:14 PM CET

## QL 3 SAKH10

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 2 mm    | Depth (inches)  | 0.079 inch |
| Height     | 6 mm    | Height (inches) | 0.236 inch |
| Width      | 26.8 mm | Width (inches)  | 1.055 inch |
| Net weight | 2.88 g  |                 |            |

## Temperatures

|                     |                |
|---------------------|----------------|
| Storage temperature | -25 °C...55 °C |
|---------------------|----------------|

## Material data

|          |       |        |      |
|----------|-------|--------|------|
| Material | Cu Zn | Colour | grey |
|----------|-------|--------|------|

## System specifications

|         |                 |
|---------|-----------------|
| Version | Cross-connector |
|---------|-----------------|

## Additional technical data

|                          |                 |                     |                 |
|--------------------------|-----------------|---------------------|-----------------|
| Explosion-tested version | No              | Installation advice | Direct mounting |
| Type of fixing           | when screwed in | Type of mounting    | when screwed in |

## Cross-connector

|                                     |      |                       |                 |
|-------------------------------------|------|-----------------------|-----------------|
| Number of cross-connected terminals | 3    | Rated current, 2-pole | 47 A            |
| Rated current, multi-pole           | 36 A | Type                  | Cross-connector |

## Dimensions

|                 |       |
|-----------------|-------|
| Pitch in mm (P) | 14 mm |
|-----------------|-------|

## General

|                     |                 |                 |   |
|---------------------|-----------------|-----------------|---|
| Installation advice | Direct mounting | Number of poles | 3 |
|---------------------|-----------------|-----------------|---|

## Rating data

|               |      |
|---------------|------|
| Rated current | 36 A |
|---------------|------|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000489    | ETIM 7.0    | EC000489    |
| ETIM 8.0    | EC000489    | ETIM 9.0    | EC000489    |
| ECLASS 9.0  | 27-14-11-40 | ECLASS 9.1  | 27-14-11-40 |
| ECLASS 10.0 | 27-14-11-40 | ECLASS 11.0 | 27-14-11-40 |
| ECLASS 12.0 | 27-14-11-40 | ECLASS 13.0 | 27250303    |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## QL 3 SAKH10

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

|                    |   |
|--------------------|---|
| Engineering Data   | <a href="#">CAD data – STEP</a>                 |
| User Documentation | <a href="#">StorageConditionsTerminalBlocks</a> |
| Catalogues         | <a href="#">Catalogues in PDF-format</a>        |