

## **Fine Wire Disc Thermocouple, PFA with Bare Tails- ANSI**



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO 9001 accredited.

## Specifications

<b>General Description</b>	Exposed junction thermocouple with Copper Disc brazed at tip
<b>Sensor Type</b>	Copper disc, 6.35mm diameter x 0.3mm thick
<b>Thermocouple Type</b>	Type K
<b>Thermocouple Junction</b>	Grounded measuring junction
<b>Cable Length</b>	2m
<b>Cable Type</b>	1/0.2mm PFA Teflon® insulated twisted wire
<b>Termination Type</b>	Bare tails
<b>Max. Temperature</b>	200°C
<b>Min. Temperature</b>	0°C
<b>Standards Met</b>	ANSI MC96.1
<b>Colour</b>	Positive: Red / Negative: Yellow
<b>Accessories</b>	Supplied with high temperature adhesive kapton strips (13x18mm x 5) for quick and easy attachment to surface/process
<b>Manufacturers Code</b>	Z2-K-2-T-DISC-ANSI

## Ordering Information

Type	Cable Length	Termination	Manufacturers Code	Manufacturers Order Code
K	2m	Bare Tails	Z2-K-2-T-DISC-ANSI	XE-0571-001