

Mineral Insulated Thermocouple with Plain Pot Seal and PFA Insulated ANSI Lead - Type K



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO 9001 accredited.

Specifications

General Description	Highly flexible, sheath can be bent/formed to suit many applications and processes
Thermocouple Type	K
Thermocouple Junction	Insulated hot junction
Probe Diameter / Length	1.5mm x 150mm
Sheath Material	310 stainless steel sheath
Pot Type	Plain pot seal (200°C)
Cable Length	1m
Cable Type	PFA Teflon® insulated flat pair cable and tails (colour coded to ANSI MC96.1)
Core / Strands	7/0.2mm
Cable Termination	Bare Tails
Max. Temperature	+1100°C (+750°C for 1.0mm)
Standards Met	colour coded to ANSI MC96.1

Ordering Information

Type	Size	Cable Length	Termination	Manufacturers Order Code
K	1.5mm x 150mm	1m	Bare Tails	XE-3025-001