

Silicone Rubber Patch Thermocouple Type K PFA Twin Twisted with Bare Tails - IEC



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO 9001 accredited.

Specifications

General Description	Resistant to many oils & chemicals
Sensor Type	Thermocouple junction encapsulated in a silicone rubber patch with self-adhesive aluminium foil backing
Thermocouple Type	Type K
Cable Length	1m
Cable Type	PFA insulated twin-twist wire 1/0.2mm
Termination Type	Bare tails
Max. Temperature	+150°C
Min. Temperature	-50°C
Standards Met	IEC
Dimensions	Length 40mm x Width 13mm x Height 5mm Rubber patch
Manufacturers Code	SRS-K-1M-T-I

Ordering Information

Thermocouple Type	Cable Length	Termination	Manufacturers Code	Manufacturers Order Code
K	1m	Bare Tails	SRS-K-1M-T-I	XE-3450-001