

IEC PFA insulated Twin Twisted Exposed Junction Thermocouple with Miniature Plug - Type K



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO 9001 accredited.

Specifications

General Description	Fast response, welded exposed junction
Sensor Type	Exposed Junction
Thermocouple Type	K
Cable Length	5m
Cable Type	Teflon® PFA insulated twin-twisted lead
Core / Strands	1/0.315mm
Termination Type	Miniature flat pin plug, colour coded in accordance IEC 584
Max. Temperature	+250°C
Min. Temperature	-75°C
Tolerance	Class 1
Standards Met	IEC-584-3
Connector Type	Plug
Connector Size	Miniature
Manufacturers Code	Z2-K-5.0-MP-1/0.315

Type	Style	Material	Cable Size	Length	Termination	Manufacturers Order Number
K	TWISTED	PFA	1/0.315mm	5m (16.4 ft)	Miniature Plug	XE-3530-001