

General Purpose Pt100 Silicone Rubber Lead - Type RTD / PRT



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO 9001 accredited.

Specifications

General Description	Suitable for general purpose industrial & commercial use
Sensor Type	Pt100 (100 Ohms @ 0°C) to IEC 751, Class B, 4 wire
Probe Diameter	6.0mm
Probe Length	50mm
Sheath Material	316 stainless steel sheath.
Cable Length	2m
Cable Type	flexible silicone rubber insulated
Core / Strands	7/0.2mm
Cable Termination	Bare Tails
Termination Type	4-wire tails allows connection to any PT100 instrument 2, 3 or 4 wire
Max. Temperature	+200°C
Min. Temperature	-50°C
Accuracy	Class B
Number of Wires	4

Ordering Information

Type	Size	Cable Length	Termination	Manufacturers Order Code
PRT	6.0mm x 50mm	2m	Bare tails	XE-3630-001