

Pt100 Class B Sensors with Teflon insulated lead - Type RTD / PRT



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO 9001 accredited.

Specifications

Sensor Type	Pt100 element in a 3.0mm diameter 316 stainless steel probe
Element	Pt100 element to IEC 751 Class B
Probe Diameter	3.0mm
Probe Length	50mm
Sheath Material	316 stainless steel probe
Cable Length	1m
Cable Type	Teflon® insulated twisted lead
Core / Strands	7/0.16mm
Cable Termination	Bare Tails
Max. Temperature	+200°C
Min. Temperature	-50°C
Standards Met	IEC 751
Accuracy	Class B

Ordering Information

Type	Size	Cable Length	Termination	Manufacturers Order Code
PRT	3.0mm x 50mm	1m	Bare tails	XE-3664-001