

Fabricated Grounded Thermocouple in Stainless Steel Tube, Glassfibre stainless steel Overbraided cable - IEC



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO 9001 accredited.

Specifications

General Description	316 stainless steel tube in various sizes
Thermocouple Type	K
Thermocouple Junction	Grounded at tip for fast response
Cable Length	2m
Cable Type	Glassfibre stainless steel overbraided cable
Cable Termination	Bare Wire Tails
Max. Temperature	+350°C
Min. Temperature	-60°C
Standards Met	IEC
Tube Diameter	4mm
Tube Length	40mm
Manufacturers Code	FAA-GSK-4.0-40-NP-2.0-C4-T-I

Ordering Information

Type	Cable Length	Diameter x Length	Termination	Manufacturers Code	Manufacturers Order Code
K	2m	4 x 40mm	Bare Tails	FAA-GSK-4.0-40-NP-2.0-C4-T-I	XE-5546-001