

ANSI High Temperature Glassfibre Twin Twisted Exposed Welded Tip Thermocouples with Standard Plug Termination



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO 9001 accredited.

Specifications

General Description	Fast response welded exposed junction. Good temperature resistance (not suitable in fluids).
Thermocouple Type	K
Thermocouple Junction	Exposed
Cable Length	5m
Cable Type	high temperature glassfibre insulated twisted cable
Core / Strands	1/0.711mm conductors (21awg)
Cable Termination	Standard plug termination
Max. Temperature	+700°C
Min. Temperature	0°C
Tolerance	Tolerance to ANSI MC96.1 Class 2
Standards Met	Colour code to ANSI MC96.1
Manufacturers Code	Z3-K-5.0-C36-SP-ANSI

Ordering Information

Type	Style	Material	Cable Size	Length	Termination	Manufacturers Order Number
K	TWIN TWISTED	GLASSFIBRE	1/0.711mm	5m (16.4 ft)	Standard Plug	XE-5630-001