

General Purpose Pt100 Probe with PFA lead - Type RTD / PRT



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO 9001 accredited.

Specifications

General Description	Multipurpose Pt100 Probe to IEC751
Sensor Type	Pt100 (100 Ohms @ 0°C) to IEC 751, Class B, 4 wire
Sheath Material	316 stainless steel sheath.
Probe Diameter	4mm
Probe Length	25mm
Cable Length	2 metre flexible Teflon® insulated, screened
Termination Type	4-wire tails allows connection to any PT100 instrument 2, 3 or 4 wire
Max. Temperature	+250°C
Min. Temperature	-50°C
Standards Met	IEC751
Accuracy	Class B

Ordering Information

Type	Size	Cable Length	Termination	Manufacturers Order Code
PRT	4.0mm x 25mm	2m	Bare tails	XE-3610-001