



| WSW P/N | L(mm) |
|--------------------|---------|
| AK500/14-OE-11-0.5 | 500±20 |
| AK500/14-OE-11-1 | 1000±20 |
| AK500/14-OE-11-1.5 | 1500±20 |
| AK500/14-OE-11-2 | 2000±20 |



Hank Dimension



NOTES:

Material:

- 1.SJT 3x14AWG(2.08MM²) VW-1, 60°C 300V.
- 2.Jacket Color: Black.
- 3.E-Green, L-Black, N-White.

Electrical Test:

- 1.100% Open & Short Testing.
- 2.Insulation Resistance: 100MΩ(Min).
- 3.Voltage: 500V DC/1Min.

RoHS compliant
Unit: mm

| Scale | Free | | | | Date | Name | Customer-No. |
|-----------|------|-----|---|------------|----------|-----------------------------------|--|
| TOLERANCE | | | | | Drawn | 26.10.2018 | Segal |
| | | | | | Approved | 18.01.2022 | Luca |
| | | | | | | | ASSMANN WSW-No. AK500/14-OE-11-x |
| DIM | TOL | ① | Update dimension & printing Remove label | 18.01.2022 | Luca | Drawing-No. ASS 8380 CA | |
| | | ② | Drawn | 26.10.2018 | Segal | rev01 | |
| Angle | TOL | Id. | Modification | Date | Name | Replace | Sheet |

